






FOCAL LENGTH (EFL): 40 ±0,4
BACK FOCAL LENGTH (BFL): 37,79

1 BLACKENED SURFACE


SURFACE A			SURFACE B		SURFACE C		
Øe 9			Øe 9		Øe 9		
			CEMENT: NOA 61 OR EQUIVALENT				
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY							
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN: mm		TITLE 10mm Dia, x 40mm FL, VIS 0, Inked, Achromatic Lens		
INDICATIONS IN ACCORDANCE WITH ISO 10110					DWG NO 63709INK		SHEET SIZE A4



- 1 AR COATING: VIS 0°
R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 23,66±0,024 CX Øe 9 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-BK7 517/642	R 18,11±0,018 CX Øe 9 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®					
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE 10mm Dia, x 40mm FL, VIS 0, Inked, Achromatic Lens					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm				DWG NO 63709INK		SHEET SIZE A4	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING										
INDICATIONS IN ACCORDANCE WITH ISO 10110										



- 1 AR COATING: VIS 0°
R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 18,11±0,018 CV Øe 9 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-SF5 673/322	R 55,78±0,056 CX Øe 9 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 587,6nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

10mm Dia, x 40mm FL, VIS 0, Inked,
Achromatic Lens

DWG NO

63709INK

SHEET SIZE
A4

SHEET
3 OF 3