

[Tous les Produits](#) / [Caméras](#) / [Caméras Gigabit Ethernet](#)

Caméras GigE Allied Vision Prosilica, Série GT See More by [Allied Vision](#)



- Caméras PoE (Power over Ethernet) résistantes pour des environnements extrêmes
- Contrôle iris précis (P-Iris) et diaphragme DC
- Résolution jusqu'à 31,4 mégapixels
- Options de montures C, F et TFL

Spécifications

Caractéristiques du produit

Fabricant: Allied Vision | **Série de Caméras:** Prosilica GT

Propriétés physiques et mécaniques

Logement: Full

Capteur

Tampon d'Image: 128MB

Capteur: Progressive Scan CMOS

Type d'Obturbateur: Global

Machine Vision Standard: GigE Vision V1.2, GenICam SFNC V1.2.1

Connectivité matérielle & interfaçage

Interface: GigE (PoE)

Connecteur: GigE, RJ45 with Screw Locks

Alimentation d'Énergie:

Power Supply Required and Sold Separately:
USA: [#15-281](#)
Europe: [#15-281](#)
Japan: [#15-281](#)
China: [#15-281](#)

GPIOs: 1 opto-isolated input, 2 opto-isolated outputs, 1 non-isolated input, 2 non-isolated outputs

Synchronisation:

Hardware Trigger (GPIO) or Software Trigger

Orientation du Port d'Interface: Back Panel

GPIO Connector Type:

12-pin Hirose (HR10)

Filetage & montage

Filetage: 1/4-20 with Tripod Mount Adapter [#87-412](#)

Environnement & durabilité

Température d'Utilisation (°C): -20 to +65

Température de Stockage (°C): -20 to +70

Informations techniques

Produits

Type	Numéro de Modèle	Type de Capteur	Résolution (MegaPixels)	Connecteur	Monture	Numéro de Stock	Prix	Achat
Monochrome Camera	GT 2000 B	2/3"	2.20	GigE, RJ45 with Screw Locks	C-Mount	#87-079	€1.960,00	Contact
Color Camera	GT 2000 C	2/3"	2.20	GigE, RJ45 with Screw Locks	C-Mount	#87-080	€1.960,00	Contact
NIR Camera	GT 2000 NIR	2/3"	2.20	GigE, RJ45 with Screw Locks	C-Mount	#88-475	€2.080,00	1 In Stock
Monochrome Camera	GT 1930 B	1/1.2"	2.40	GigE, RJ45 with Screw Locks	C-Mount	#34-201	€2.010,00	1 In Stock
Color Camera	GT 1930 C	1/1.2"	2.40	GigE, RJ45 with Screw Locks	C-Mount	#34-202	€2.010,00	1 In Stock
Color Camera	GT 2050 C	1"	4.20	GigE, RJ45 with Screw Locks	C-Mount	#87-082	€2.810,00	Contact
Monochrome Camera	GT 2050 B	1"	4.20	GigE, RJ45 with Screw Locks	C-Mount	#87-081	€2.810,00	Contact
Monochrome Camera	GT 2460 B	2/3"	5.10	GigE, RJ45 with Screw Locks	C-Mount	#13-943	€2.360,00	2 In Stock
Color Camera	GT 2460 C	2/3"	5.10	GigE, RJ45 with Screw Locks	C-Mount	#13-944	€2.360,00	1 In Stock
Monochrome Camera	GT 4400	4/3"	19.60	GigE, RJ45 with Screw Locks	C-Mount	#14-709	€5.620,00	Contact
Color Camera	GT 4400	4/3"	19.60	GigE, RJ45 with Screw Locks	C-Mount	#14-710	€5.730,00	Contact
Monochrome Camera	GT 4400	4/3"	19.60	GigE, RJ45 with Screw Locks	TFL-Mount	#14-711	€5.620,00	Contact
Color Camera	GT 4400	4/3"	19.60	GigE, RJ45 with Screw Locks	TFL-Mount	#14-712	€5.730,00	Contact
Monochrome Camera	GT 5400	4/3"	16.80	GigE, RJ45 with Screw Locks	C-Mount	#14-713	€5.060,00	Contact

Color Camera	GT 5400	4/3"	16.80	GigE, RJ45 with Screw Locks	C-Mount	#14-714	€5.170,00	Contact
Monochrome Camera	GT 5400	4/3"	16.80	GigE, RJ45 with Screw Locks	TFL-Mount	#14-715	€5.060,00	Contact
Color Camera	GT 5400	4/3"	16.80	GigE, RJ45 with Screw Locks	TFL-Mount	#14-716	€5.170,00	Contact
Monochrome Camera	GT 5120	APS-H	26.20	GigE, RJ45 with Screw Locks	F-Mount	#14-738	€7.280,00	Contact
Monochrome Camera	GT 6400	APS-C	31.40	GigE, RJ45 with Screw Locks	F-Mount	#14-717	€7.080,00	1 In Stock
Color Camera	GT 6400	APS-C	31.40	GigE, RJ45 with Screw Locks	F-Mount	#14-718	€7.190,00	1 In Stock
Monochrome Camera	GT 6400	APS-C	31.40	GigE, RJ45 with Screw Locks	TFL-Mount	#14-719	€7.080,00	Contact
Color Camera	GT 6400	APS-C	31.40	GigE, RJ45 with Screw Locks	TFL-Mount	#14-720	€7.190,00	Contact



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Téléphone: 1-800-363-1992 :
www.edmundoptics.com