

[Tous les Produits](#) / [Sources Lumineuses et Éclairages](#) / [Éclairages pour la Vision Industrielle](#) / [Anneaux Lumineux](#)

Anneaux Lumineux LED à Grand Angle de CCS See More by [CCS](#)



- Éclairage direct à grand angle pour une intensité uniforme
- Conçus pour une puissance de sortie constante sur des périodes de fonctionnement prolongées
- Idéaux pour l'éclairage à fond clair en ligne

Spécifications

Caractéristiques du produit


Type d'Éclairage:	LED Illuminator	Fabricant:	CCS
Géométrie:	High-Angle Ring Light	Mode d'Éclairage:	Constant

Connectivité matérielle & interfaçage

Tension d'Entrée (V):	24	Alimentation d'Énergie:	Power Supply Required and Sold Separately: USA: #73-491 Europe: #73-491 Japan: #89-513 Korea: #33-773 China: #73-491
-----------------------	----	-------------------------	---

Informations techniques

➤ Imaging Example: Imaging Electrodes of Electronic Parts



Description	Visual inspection
Workpiece	Electronic parts
Conventional lighting	LED Bar Light
New lighting	LDR2-32RD2
Result	Improved uniformity

Workpiece image




Electronic parts

LED Bar Light




It's difficult to make an image of the electrode part using a Bar Light.

LDR2-32RD2



A Ring Light can illuminate the electrode part evenly and make an image.

➤ Imaging Example: Imaging Text on Intake Valves



Description	Character recognition
Workpiece	Intake valves (automobile parts)
Conventional lighting	LED Ring Light
New lighting	LDR2-50RD2
Result	Emphasized characters

Workpiece image



Intake valves

LED Ring Light



It's difficult to clearly recognize the text due to the inner indentation.

LDR2-50RD2



Allows for image that makes the character edges stand out.

Produits

Couleur	Longueur d'Onde (nm)	Consommation de Puissance (W)	Dimensions (mm)	Numéro de Stock	Prix	Achat
IR	850.00	3.8	OD: 50, ID: 28, Height: 16	#21-839	€925,00	2 In Stock
IR	940.00	3.8	OD: 50, ID: 28, Height: 16	#21-840	€925,00	2 In Stock
Red	630.00	3.1	OD: 50, ID: 28, Height: 16	#21-777	€705,00	1 In Stock
White	-	3.8	OD: 50, ID: 28, Height: 16	#21-778	€925,00	2 In Stock
Blue	470.00	3.8	OD: 50, ID: 28, Height: 16	#21-779	€925,00	2 In Stock
Red	630.00	6.1	OD: 70, ID: 35, Height: 22	#21-780	€585,00	Contact
White	-	7.6	OD: 70, ID: 35, Height: 22	#21-781	€1.070,00	2 In Stock
Blue	470.00	7.6	OD: 70, ID: 35, Height: 22	#21-782	€1.070,00	6 In Stock
Red	630.00	11	OD: 90, ID: 50, Height: 20	#21-783	€1.455,00	2 In Stock
White	-	14	OD: 90, ID: 50, Height: 20	#21-784	€1.780,00	Contact
Blue	470.00	14	OD: 90, ID: 50, Height: 20	#21-785	€1.780,00	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Téléphone: 1-800-363-1992 :

www.edmundoptics.com