

Kit de Démarrage Labo, Métrique



Lab Starter Kit (Not all products shown)

Stock **#37-090** [CONTACT](#)

⊖ 1 ⊕ €9.990⁰⁰

AJOUTER AU PANIER

Prix sur Quantité

Qté 1+	€9.990,00 prix unitaire
Need More?	Demande de Devis

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Caractéristiques du produit

Contenu du Coffret:

See Technical Information tab for a detailed list of items included in the kit

Conformité réglementaire

Certificate of Conformance:

[Visionner](#)

Description produit

- Point de Départ Idéal pour les Nouveaux Laboratoires
- 255 Pièces Individuelles Incluses
- Optique, Optomécanique, Nettoyage, Outils et plus Encore
- Des Versions de Montage Impériales et Métriques sont Disponibles.

Le kit de Démarrage Labo est idéal pour l'approvisionnement d'un tout nouveau laboratoire. Le kit contient des produits essentiels utiles pour tout laboratoire, depuis l'optique jusqu'aux détecteurs, au nettoyage et aux outils. Vous y trouverez également une gamme de lentilles, de filtres et de prismes conçus principalement pour le spectre du visible. Le Kit de Démarrage Labo est également livré avec deux sources lumineuses, une LED blanche, et un module de diode laser Stingray cohérent haute performance de 640 nm. Des versions de montage impériales et métriques sont disponibles, contenant des optomécaniques et des outils compatibles avec les optiques incluses.

Informations techniques

	Description	Stock No.	Quantity
Optics	Optical Component Kit	#55-486	1
	25mm Simple Lens Kit	#48-613	1
	25mm Achromat Kit MgF ₂	#52-306	1
	VIS, 25nm, 25mm Dia. Filter Kit	#88-300	1
	25mm Dia., Absorptive ND Kit	#63-469	1
	25mm Dia., MS Colored Glass Longpass Kit	#47-399	1
Mounting	C-Mount Extension Tube Kit	#54-668	1
	C-Mount Components Kit	#55-487	1
	70mm English Linear Translation Stage	#66-428	2
	70mm Verticle Stage (0.4" Travel)	#66-503	1
	25.4mm Optics Mount	#64-561	4
	25.4mm C-Mount Optics Holder	#56-354	2
	1/4-20 English Post Kit	#68-230	1
	1/4-20 English Post Holder Kit	#68-233	1
	2" x 3" Sliding Baseplate	#03-655	5
	Pivot Base	#53-355	5
	Dove Rail 12"	#54-401	1
	Dove Rail Carrier	#55-339	1
	2' x 3' Baseplate	#03-680	1
	1" Circular Kinematic Mount	#58-851	4
	70mm Bar-Type Clamp	#03-669	1
	110mm Bar-Type Clamp	#03-666	1
	60mm Rectangular Optics Mount	#54-995	1
Fixed Filter Mount	#54-997	1	
Illumination	5mW StingRay 640nm Laser	#86-849	1
	StingRay Mounting Adapter	#86-879	1
	M-LED Illuminator	#89-740	1
	Semi-Rigid Light Guide	#54-210	1
	Light Guide Adapter	#66-908	1
Cleaning	Cleaning Kit	#62-535	1
Tools	Spanner Wrench	#11-130	1
	Optical Component Case with Drawers	#59-815	1
	English Cap Screw Kit	#56-383	1
	Metric Cap Screw Kit	#56-384	1
	M6 Male to 1/4-20 Female Adapter	#53-927	5
	1/4-20 Male to M6 Female Adapter	#53-928	5
	Metric Ball Point Hex Driver Set	#88-155	1
	English Ball Point Hex Driver Set	#34-552	1
	Tweezers Kit	#86-719	1
	Screwdriver Kit	#86-721	1

	Description	Stock No.	Quantity
Optics	Optical Component Kit	#55-486	1
	25mm Simple Lens Kit	#48-613	1
	25mm Achromat Kit MgF ₂	#52-306	1
	VIS, 25nm, 25mm Dia. Filter Kit	#88-300	1
	25mm Dia., Absorptive ND Kit	#63-469	1
	25mm Dia., MS Colored Glass Longpass Kit	#47-399	1

Mounting	C-Mount Extension Tube Kit	#54-668	1
	C-Mount Components Kit	#55-487	1
	70mm, Center Drive, Standard Top, Metric Extended Micrometer	#66-434	2
	70mm, Metric Micrometer Z-Stage	#66-505	1
	25.4mm Optics Mount	#64-561	4
	25.4mm C-Mount Optics Holder	#56-354	2
	Metric Post Kit, M6 Stud	#68-232	1
	Metric Post Holder Kit	#68-234	1
	85 x 50mm English Base Plate	#58-998	5
	Pivot Base	#53-355	5
	12" Dovetail Optical Rail	#54-928	1
	Dove Rail Carrier	#54-931	1
	900mm x 600mm, Breadboard	#87-214	1
	1" Circular Kinematic Mount	#58-851	4
	70mm Bar-Type Clamp	#03-669	1
	110mm Bar-Type Clamp	#03-666	1
	60mm Rectangular Optics Mount	#54-995	1
	Fixed Filter Mount	#54-997	1
Illumination	5mW StingRay 640nm Laser	#86-849	1
	StingRay Mounting Adapter	#86-879	1
	M-LED Illuminator	#89-740	1
	Semi-Rigid Light Guide	#54-210	1
	Light Guide Adapter	#66-908	1
Cleaning	Cleaning Kit	#62-535	1
Tools	Spanner Wrench	#11-130	1
	Optical Component Case with Drawers	#59-815	1
	English Cap Screw Kit	#56-383	1
	Metric Cap Screw Kit	#56-384	1
	M6 Male to 1/4-20 Female Adapter	#53-927	5
	1/4-20 Male to M6 Female Adapter	#53-928	5
	Metric Ball Point Hex Driver Set	#88-155	1
	English Ball Point Hex Driver Set	#34-552	1
	Tweezers Kit	#86-719	1
	Screwdriver Kit	#86-721	1