


Cristal non linéaire BBO Type I, 10 x 10 x 0,5 mm, 800 nm SHG



Mounted Type I BBO Nonlinear Crystal

Stock #11-166 3-4 JOURS

⊖ 1 ⊕ **€895,00**

AJOUTER AU PANIER

Qté 1-2

€895,00

Qté 3+

€790,00

Prix sur Quantité

[Demande de Devis](#)

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Type de Cristal:
BBO

Longueur d'Onde de Conception DWL (nm):
800

Ouverture Utile CA (mm):
9.40

Dimensions (mm):
10.0 x 10.0 +0.0/-0.1

Épaisseur (mm):
0.50 +0.0/-0.1

Chanfrein de Protection:
<0.1mm x 45°

Orientation Θ/Φ (°):
29.2/90

Traitement:
AR Coating

Spécification du Traitement:
S1: 400 - 800nm Broadband Protective Coating
S2: 400 - 800nm Broadband Protective Coating

Parallélisme (arcsec):
<20

Perpendicularity (arcmin):
<5

Qualité de Surface:
20-10

Planéité de Surface (P-V):
λ/8

Monture:
Mounted

Mount Diameter (mm):
25.4

Épaisseur de Monture (mm):
5 (unthreaded)

Applications Typiques:
SHG @ 800nm, Type I

Type:
Nonlinear Crystal

Damage Threshold, By Design:
10 J/cm² @ 1064nm, 10ns, 10Hz

Remarque:
Mount is 25.4mm Dia., 5mm Thick Unthreaded Black
Anodized Metal Mount (see drawing for more
information)

Conformité réglementaire

RoHS 2015:
[Conforme](#)

Certificate of Conformance:
[Visionner](#)

Reach 240:
[Conforme](#)