

In order to provide more accurate inventory information, please select your shipping country.

Sélectionner votre Pays/Région:

European Union

SUBMIT



Optotune Fast Steering Mirror, Protected Silver Coated



+1

Stock #14-574 3-4 JOURS

- 1 +

€2.544,00

AJOUTER AU PANIER

Qté 1+

€2.544,00

Prix sur Quantité

[Demande de Devis](#)

Les prix sont indiqués hors TVA et droits applicables.

Remarque : Des accessoires sont nécessaires pour toute utilisation. | [En savoir plus](#)

Espace téléchargement

Numéro de Modèle:
MR-15-30-PS-25x25D

Diamètre (mm):
15.00

Diamètre du Logement (mm): 45
Traitement: Protected Silver
Spécification du Traitement: R _{avg} >94% @450 - 750nm
Qualité de Surface: 60-40
Mechanical Tilt (°): ±25
Répétabilité (μrad): 30 - 100 RMS
Température de Stockage (°C): -40 to +85
Température d'Utilisation (°C): 0 to +40
Système d'Utilisation: Windows® 10
Alimentation: 15 - 28 VDC
Alimentation d'Énergie: Power Supply Required and Sold Separately. USA: #14-576 Europe: #14-576 Japan: Not Available Korea: Not Available China: #14-576
Remarque: Do not connect or disconnect the mirror head while the base unit is connected to power as this will damage the mirror driver.
Angle Balayé (°): ±25 (Mechanical) ±50 (Optical)
Step Response 0.1° (ms): 2
Step Response 20° (ms): 12

Conformité réglementaire

RoHS 2015: Conforme
Reach 224: Conforme
Certificate of Conformance: Visionner