

In order to provide more accurate inventory information, please select your shipping country:

Sélectionner votre Pays/Région:

European Union

SUBMIT

25,4mm dia X 50,8mm FL



High Precision Laser Grade Aspheric Lenses

Stock #39-558

3-4 JOURS

[D'autres traitements](#)



1



€825,00

AJOUTER AU PANIER

Qté 1+

€825,00

Prix sur Quantité

[Demande de Devis](#)

!

 Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement



Diamètre (mm):
25.40 +0.00/-0.05

Distance Focale EFL (mm):
50.80 @ 532nm

Ouverture Numérique NA:

0.25
Distance Focale Arrière BFL (mm): 45.36
Substrat: ☐ Fused Silica (Coming 7980)
Longueur d'onde de conception asphérique: 532
Erreur de forme asphérique, RMS à 632,8 nm: $\lambda/40$
Traitement: Laser V-Coat (532nm)
Spécification du Traitement: R _{abs} <0.25% @ 532nm
Centrage (arcmin): <1
Qualité de Surface: 10-5
Ouverture Utile CA (mm): 21.40
Épaisseur au Bord ET (mm): 4.40
Épaisseur Centrale CT (mm): 7.90
f/#: 2
Biseau: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Strehl Ratio: >0.8
Taille de Spot (µm): See Technical Information Tab
Conjugate Distance: Infinite
Remarque: Strehl Ratio is >0.8 by design and tested
Damage Threshold, By Design: ☐ 10 J/cm^2 @ 532nm, 20ns, 20Hz
Puissance (Dioptries): 19.69

Conformité réglementaire

RoHS: Conforme
Certificate of Conformance: Visionner