

TECHSPEC®

Film Polarisant Linéaire (XP42-75), 50 mm de dia.



Stock **#19-017** FIN DE SÉRIE 3-4 JOURS

-

1

+

€14,95

AJOUTER AU PANIER

Qté 1+

€14,95

Prix sur Quantité

[Demande de Devis](#)

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Diamètre (mm):
50.00

Rapport d'Extinction:
9000:1 (nominal at 555nm)

Substrat: ☐
[Polymer Film XP42-75](#)

Température d'Utilisation (°C):
-40 to +80

Épaisseur (mm):
0.77 ±0.08

Transmission (%) : Single: 42 ±2 Parallel: 36.4 Crossed: <0.004 (nominal at 555nm)
Type : Linear Polarizer
Tolérance Dimensionelle (mm) : +0.0/-0.5
Construction : Polarizing Film
Remarque : Polarization axis can be identified as follows: Circular Parts - Parallel to direction of notch on polarizer Square Parts - Parallel to mark on protective film Rectangular Parts - Parallel to first listed dimension
Gamme de Longueur d'Onde (nm) : 400 - 700
Efficacité de la polarisation (%) : >99.98 (nominal at 555nm)
Transmission Variance after 1000 Hours (%) : <±5
#Sorting : 29.00

Conformité réglementaire

RoHS 2015 : Conforme
Certificate of Conformance : Visionner
Reach 235 : Conforme