


In order to provide more accurate inventory information, please select your shipping country.

Sélectionner votre Pays/Région: European Union

SUBMIT

Cristal non lineaire BBO Type I, 6 x 6 x 0,5 mm, 800 nm THG



Mounted Type I BBO Nonlinear Crystal

Stock #11-168 3-4 JOURS



1



€525,00

AJOUTER AU PANIER

Qté 1-2

€525,00

Qté 3+

€465,00

Prix sur Quantité

[Demande de Devis](#)

⚠ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Type de Cristal:
BBO

Longueur d'Onde de Conception DWL (nm):
800

Ouverture Utile CA (mm):
5.70

Dimensions (mm): 6.0 x6.0 +0.0/-0.1
Épaisseur (mm): 0.50 +0.0/-0.1
Chanfrein de Protection: <0.1mm x45°
Orientation Θ/Φ (°): 44.3/90
Traitement: AR Coating
Spécification du Traitement: S1: 400 - 800nm Broadband Protective Coating S2: 266nm Protective Coating
Parallélisme (arcsec): <20
Perpendicularity (arcmin): <5
Qualité de Surface: 20-10
Planéité de Surface (P-V): $\lambda/8$
Monture: Mounted
Mount Diameter (mm): 25.4
Épaisseur de Monture (mm): 6 (unthreaded)
Applications Typiques: THG @ 800nm, Type I
Type: Nonlinear Crystal
Damage Threshold, By Design: ☐ 10 J/cm ² @ 1064nm, 10ns, 10Hz
Remarque: Mount is 25.4mm Dia., 6mm Thick Unthreaded Black Anodized Metal Mount (see drawing for more information)

Conformité réglementaire

RoHS 2015: Conforme
Certificate of Conformance: Visionner
Reach 235: Conforme