

[Afficher tous les 33 produits de la même famille.](#)

Kit de Développement pour Lentilles Liquides à Focalisation Variable Corning® Varioptic®, ouverture utile de 5,8 mm



5.8mm CA, Corning® Varioptic® Variable Focus Liquid Lens Development Kit



Stock #16-034 FIN DE SÉRIE 3-4 JOURS

- 1 +

€601,95

AJOUTER AU PANIER

Qté 1+

€601,95

Prix sur Quantité

[Demande de Devis](#)

Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement



Diamètre (mm):
15.50 (packaged lens, 13.00 bare lens)

Traitement:
VS

Type: Development Kit
Ouverture Utile CA (mm): 5.8
Contenu du Coffret: Corning® Varioptio® A-58N0 Lens (without cable) A-58N0-P19 Lens (with bent flex cable) Maxim MAX14574 Driver Board (with 4 pin connector and 6 pin connector for thermistor populated 6 pin FPC) USB-MFlexiboard (with 4 and 6 pin connector and USB compatibility) M4 thread holder for lens Bent Flex Cable FPC-A-19 Control Software Documentation Package
Gamme de Focalisation: -5 to +10 diopter
Numéro de Modèle: D-A-58N0
Température d'Utilisation (°C): -20 to +50
Température de Stockage (°C): -40 to +85
Épaisseur (mm): 6.30 (packaged lens, 4.30 bare lens)
Transmission (%): 97 @ 587nm
Erreur du Front d'Onde Transmis, RMS: 80nm
Applications Typiques: Optical instruments such as ophthalmology, scientific instrumentation, life sciences and microscopes requiring a larger clear aperture than the A-39N lens

Conformité réglementaire

RoHS 2015: Dispensé
Reach 224: Contains SVHC(s)
Certificate of Conformance: Visionner