

TECHSPEC® Miroir Laser Ultrarapide Traité Argent Amélioré, 600-1000 nm, 50,8 mm de dia.



Stock #13-061 3-4 JOURS

⊖ 1 ⊕ **€211,00**

AJOUTER AU PANIER

Qté 1-4
€211,00

Qté 5+
€186,00

Prix sur Quantité
Demande de Devis

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement



Qualité de Surface:
10-5

Type:
Flat Mirror

Parallélisme (arcmin):
<3

Ouverture Utile (%): 90
Surface Arrière: Commercial Polish
Spécification du Traitement: R _{avg} >99% @ 600 - 1000nm, 0° R _s >99% @ 540 - 1000nm, 45° R _p >98.5% @ ~730 - 870nm, 45°
GDD Specification: 0 ±20fs² @ 600 - 1050nm
Gamme de Longueur d'Onde (nm): 600 - 1000
Planéité de Surface (P-V): λ/10
Type de Traitement: Ultrafast-Enhanced Silver
Traitement: Ultrafast-Enhanced Silver (600-1000nm)
Diamètre (mm): 50.80 +0.00/-0.10
Épaisseur (mm): 9.53 ±0.20
Substrat: ☐ Fused Silica (Corning 7980)
Damage Threshold, Reference: ☐ 0.3 J/cm² @ 800nm, 48fs, 1 pulse (typical) 0.16 J/cm² @ 800nm, 48fs, 100Hz, 1000 pulses (typical)
Bords: Ground, protective bevel as needed

Conformité réglementaire

RoHS 2015: Conforme
Reach 223: Conforme
Certificate of Conformance: Visionner