
NOTES:


- SUBSTRATE: N-BK7
- 2. CENTERING TOLERANCE (AT 587.6nm): BEAM DEVIATION: ≤2 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE): Telecom
 - \$1, \$2, \$3, & \$4: R(AVG) <0.5% @ 1100 1620nm \$5: MULTILAYER DIELECTRIC TO ACHIEVE: TRANSMISSION > 45% ± 5% POLARIZATION < 6%

FINE GROUND SURFACE

ELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE NOA 61

6.\ MARK IDENTIFIES BEAMSPLITTED COATED RIGHT ANGLE PRISM





FOR INFORMATION ONLY:

PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

1 OF 1

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE ACCURACY	1/8 WAVE	1/8 WAVE	
SURFACE QUALITY	40-20	40-20	
CLEAR APERTURE	> 90%	> 90%	

			S [®]	
THIRD ANGLE _ PROJECTION		TITLE	15mm 1100-1620nm, Non-Polarizing Cube Beamsplitter	
ALL DIMS IN	mm	DWG NO	47235	SHEET 1 OF 1