




NOTES:

- 1. SUBSTRATE:
BOROFLOAT®
- 2. COATING PERFORMANCE (APPLY ACROSS COATING APERTURE)
T(AVG) <1.0% @ 400 - 480nm
T(AVG) >80% @ 525 - 555nm
T(AVG) <1.0% @ 590 - 720nm
T(ABS) <1.0% @ 425 - 455nm
T(ABS) >70% @ 530 - 550nm
T(ABS) <1.0% @ 620 - 690nm

3. FINE GROUND SURFACE

- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
CLEAR APERTURE	≥85%	≥85%
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	12.5mm Diameter, Green Dichroic Filter		
DWG NO	52533	SHEET 1 OF 1	