



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



32299
TUE DEC 16 2008 UNITS ARE μm .
FIELD : 1
RMS RADIUS : 8.977
GD RADIUS : 25.397
SCALE BAR : 100


REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

32299
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 59.6364 μm
DIFFRACTION LIMITED RANGE: 9.393 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

CHROMATIC FOCAL SHIFT




TRANSVERSE RAY FAN PLOT

32299
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 100.000 \mu\text{m}$.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

32299
TUE DEC 16 2008
DATA FOR 0.4000 TO 0.7000 μm .
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF



EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM