



NOTES:

- 1. SUBSTRATE: BOROFLOAT
- 2. COATING (APPLY ACROSS COATING APERTURE)
  - S1: Tavg <0.5% @ 350 - 685nm
  - Tavg >85% @ 900 - 1700 nm
  - Tavg >70% @ 710 - 900 nm and 1700 - 2500nm
  - S2: NONE
- 3. ROHS COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

	S1	S2	THIRD ANGLE PROJECTION 		TITLE	Ø12.5mm, 700nm, CUT-ON SWIR LONGPASS FILTER	
SURFACE QUALITY	80-50	80-50	ALL DIMS IN	mm	DWG NO	86445	SHEET 1 OF 1