



NOTES:

1. CONSTRUCTION: MOUNTED IN BLACK ANODIZED RING
2. COATING (APPLY ACROSS COATING APERTURE)  
  
 DURABILITY: MIL-C-48497A  
 PERFORMANCE SPECIFICATIONS:  
 CWL: 532nm & 1064nm  
 FWHM: 25 @ 532nm; 50 @ 1064nm  
  
 R (ABS) > 99.5% @ 532nm & 1064nm  
 T (ABS) < 0.001% @ 532nm & 1064nm  
 T (AVG) > 80% FROM 325 - 400nm  
 T (AVG) > 90% FROM 400 - 1200nm
3. SURFACE QUALITY: 60-40
4. TRANSMITTED WAVEFRONT DISTORTION RMS @632.8nm: 1λ
5. ROHS COMPLIANT

6. ARROW ON PART POINTS TOWARDS COATED SURFACE



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
 DO NOT MANUFACTURE  
 PARTS TO THIS DRAWING**



THIRD ANGLE PROJECTION		TITLE	OD6, Ø12.5mm, 532 & 1064nm, MULTI-NOTCH FILTER	
ALL DIMS IN	mm	DWG NO	87017	SHEET 1 OF 1