



NOTES:

1. SUBSTRATE MATERIAL  
SCHOTT: N-BK7 517/642
2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: NONE  
S2: NIR I  
Ravg ≤0.5% @ 600 - 1050nm

3. FINE GRIND SURFACE

4. RoHS COMPLIANT




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
ANGLE TOL.	±15	±15
SURFACE QUALITY	40-20	40-20
SURFACE FLATNESS	λ/8	λ/8
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION



ALL DIMS IN

mm



TITLE

50mm, NIR I COATED, BBAR COATED RIGHT ANGLE PRISM

DWG NO

84528

SHEET 1 OF 1