



TECHSPEC® ACHROMATIC LENSES



TECHSPEC® ACHROMATIC LENSES



Surface: IMA

Spot Diagram	
63710 4/24/2017 Units are μm. Field : 1 RMS radius : 1.459 GEO radius : 2.931 Scale bar : 10	Airy Radius: 3.974 μm. Legend items refer to Wavelengths Reference : Chief Ray
Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM 63710.ZMX Configuration 1 of 1	

Chromatic Focal Shift	
63710 4/24/2017 Maximum Focal Shift Range: 29.5451 μm Diffraction Limited Range: 72.225 μm Pupil Zone: 0.0000	Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM 63710.ZMX Configuration 1 of 1



Transverse Ray Fan Plot	
63710 4/24/2017 Maximum Scale: ± 5.000 μm. 0.486 0.588 0.656 Surface: Image	Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM 63710.ZMX Configuration 1 of 1

Polychromatic Diffraction MTF	
63710 4/24/2017 Data for 0.4861 to 0.6563 μm. Surface: Image Legend items refer to Field positions	Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM 63710.ZMX Configuration 1 of 1