




NOTES:

1. SUBSTRATE MATERIAL:
BOROFLOAT®
2. CLEAR APERTURE AND COATING APERTURE
ARE CENTERED ON SURFACES
3. COATING (APPLY ACROSS CLEAR APERTURE)
S1: T(avg) >90% from 425 - 675nm @ 0 AOI
R(avg) >95% from 750 - 1100nm @0 AOI

S2:NONE


4. FINE GRIND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. 001	S1	S2	Edmund Optics®			
SHAPE	PLANO	PLANO				
SURFACE QUALITY	80-50	80-50				
SURFACE FLATNESS	4 - 6λ	4 - 6λ	ALL DIMS IN mm		TITLE	25.0 x 25.0mm, 0° AOI, Hot Mirror
CLEAR APERTURE	21.25 x 21.25	21.25 x 21.25			DWG NO	43843
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				