



NOTES:

1. SUBSTRATE:
FUSED SILICA MOUNTED IN BLACK ANODIZED ALUMINUM RING
2. TRANSMITTED WAVEFRONT ERROR: $\lambda/4$
3. RoHS: COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SECTION A-A

	VALUE
CENTER WAVELENGTH (CWL) (nm)	525 ± 3nm
MINIMUM BANDWIDTH (nm)	45
FULL WIDTH HALF MAX (FWHM) (nm)	51
MINIMUM TRANSMISSION (%)	>93
OD6 BLOCKING RANGE (nm)	473 - 491
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED
DURABILITY	MIL-C-48479A, SECT. 3.4.1
ENVIRONMENTAL	MIL-STD-801F, SECT. 507 .4

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®



TITLE	OD6, Ø50mm, 525nm x 45nm, BP FLUORESCENCE FILTER		
DWG NO	86992	SHEET	1 OF 1