

## NOTES:


- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) S1 & S2: RAVG ≤1.75% @ 400 - 700nm



5. Rohs Compliant







## PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

S1 S2 SHAPE PLANO PLANO	
DI ANIO	
SHAPE PLANO PLANO	
SURFACE QUALITY 60-40 60-40	
CLEAR APERTURE Ø13.50 Ø13.50	
BEVEL PROTECTIVE AS NEEDED PROTECTIVE AS NE	EDED

	<b>EO</b> <sup>®</sup> Edmund		<b>Edmund Optic</b>	S®
THIRD ANGLE PROJECTION		TITLE	15mm DIA., 3mm THICK, MGF2 COATE N-BK7 WINDOW	D λ/4
ALL DIMS IN	mm	DWG NO	45576	SHEET 1 OF

15mm DIA., 3mm THICK, MGF2 COATED λ/4
N-BK7 WINDOW

SHEET 1 OF 1