




NOTES:

1. SUBSTRATE:
GRADE A FINE ANNEALED
- ② COATING (APPLY ACROSS COATING APERTURE)
NONE
NONE
3. CENTERING TOLERANCE (AT 587.6nm):
PLANO AXIS WEDGE: < 5 ARCMIN
POWER AXIS WEDGE: < 5 ARCMIN
AXIAL TWIST: < 3 ARCMIN
- △ 4. FINE GRIND SURFACE
5. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
6. FOCAL LENGHT (EFL): 75nm
BACK FOCAL LENGTH (BFL): 72.93nm
7. RoHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

	S1	S2
SHAPE	CONVEX	PLANO
SURFACE QUALITY	40 - 20	40 - 20
CLEAR APERTURE	Ø22.86 x 22.86	Ø22.86 x 22.86
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm

TITLE

LENS PCX CYLINDER 25.40mm x 25.40mm x
75.00mm EFL

DWG NO

34755

SHEET
1 OF 1