




NOTES:

1. SUBSTRATE : N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: ALUMINIZED
R(avg) >85% @ 400 - 700nm W/BLACK OVERPAINT
 - S2: VIS 0°
R(avg) ≤0.4% @ 425 - 675nm
3. TOLERANCES FOR UNSPECIFIED ANGLES IS ±3 ARCMIN

4. FINE GRIND SURFACE

5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
WAVELENGTH RANGE (nm)	400 - 700	400 - 700
SURFACE QUALITY	40-20	40-20
SURFACE FLATNESS	λ/8	λ/8
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION



ALL DIMS IN

mm

EO® Edmund Optics®

TITLE	25mm ALUMINIZED, SCHMIDT PRISM	
DWG NO	47260	SHEET 1 OF 1