


NOTES:

1. SUBSTRATE: FUSED SILICA
2. COATING (APPLY ACROSS CLEAR APERTURE)
 S1: R(avg) ≤1.5% @ 600 - 1050nm
 S2: R(avg) ≤1.5% @ 600 - 1050nm
3. EDGES: FINE GROUND
4. CENTERING: <3-5 ARCMIN
5. ASPHERE FIGURE ERROR: 0.75µm RMS

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



COEFFICIENT TABLE	
COEFFICIENT	S1
k	-2.050191
D	0
E	7.1228748E-5
F	-1.0688222E-7
G	3.2884865E-10
H	-3.774342E-13
J	0
L	0

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	EFL @ 587.6nm	30	Edmund Optics®
SHAPE	CONVEX	PLANO	BFL @ 587.6nm	24.17	
RADIUS	13.754	INFINITY			TITLE 25mm DIA 0.42 NA NIR COATED, UV FUSED SILICA ASPHERIC LENS
SURFACE QUALITY	60-40	60-40			
CLEAR APERTURE	90%	90%			DWG NO 49594
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			
			ALL DIMS IN	mm	SHEET 1 OF 1