



- NOTES:
- 1. SUBSTRATE: B270
 - 2. CONSTRUCTION: DICHROIC
 - 3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <3 arcmin


-  EDGE CUT
- 5. EXTINCTION RATIO: 100:1
 - 6. OPERATING TEMPERATURE (°C) : -15 to +70
 - 7. WAVELENGTH RANGE: 400 - 700nm
 - 8. RoHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1 & S2
SHAPE	PLANO
SURFACE FLATNESS	4 - 6λ
SURFACE QUALITY	80-50
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 Edmund Optics®	
TITLE	41mm DIA. Unmounted Linear Glass Polarizing Filter
DWG NO	53345
SHEET 1 OF 1	