



NOTES:

- SUBSTRATE: L-BAL35
- COATING (APPLY ACROSS CLEAR APERTURE)
S1: R(avg) ≤1.5% @ 425 - 675nm
S2: R(avg) ≤1.5% @ 425 - 675nm
- EDGES: FINE GROUND
- CENTERING: 3-5 ARCMIN
- ASPHERE FIGURE ERROR: 0.75 μm RMS

△ 6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(1/RADIUS)^*Y^2}{1 + \sqrt{1 - (1+k)*(1/RADIUS)^2*Y^2}} + D*Y^2 + E*Y^4 + F*Y^6 + G*Y^8 + H*Y^{10} + J*Y^{12} + L*Y^{14}$$




COEFFICIENT TABLE △ 6.

COEFFICIENT	S1
SEMI-DIAMETER	12.500000E+00
(1/RADIUS)	3.394779E-02
k	-7.100000E-01
D	0.000000E+00
E	5.839810E-07
F	0.000000E+00
G	0.000000E+00
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	EFL @ 587.6μm	50	 Edmund Optics®			
SHAPE	CONVEX	PLANO	BFL @ 587.6μm	46.54				
RADIUS	29.457	INFINITY	THIRD ANGLE PROJECTION 		TITLE	25mm DIA, 0.25 NUMERICAL APERTURE, VIS COATED, ASPHERIC LENS		
SURFACE QUALITY	60-40	60-40						
CLEAR APERTURE	90%	90%	ALL DIMS IN mm		DWG NO	33945		SHEET 1 OF 1
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED						