



NOTES:

1. SUBSTRATE:
α-BBO
2. BEAM DEVIATION: <3 ARCMIN
3. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

WAVEFRONT DISTORTION	$\lambda/2$ @ 632.8 nm
DAMAGE THRESHOLD, PULSED	5 J/cm ² , 10ns, 10 Hz @ 1064 nm
WAVELENGTH RANGE (nm)	200 - 350
SURFACE QUALITY	20-10
EXTINCTION RATIO	< 0.000005



ALL DIMS IN mm



TITLE	GLAN-LASER POLARIZER 220 - 350nm, 12.7mm		
DWG NO	89554	SHEET	1 OF 1