NOTES:

1. SUBSTRATE SAPPHIRE (AI2O3)

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING


- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 3.5 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


S1: R(AVG) ≤ 0.5% FROM 600-1050nm @ 0° AOI

S2: R(AVG) ≤ 0.5% FROM 600-1050nm @ 0° AOI

4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

5. ROHS COMPLIANT





	S1	\$2	SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY				
SHAPE	PLANO	PLANO				®	
CLEAR APERTURE	Ø22.5	Ø22.5				Edmund Optics	R
SURFACE FLATNESS	2λ	2λ					>
SURFACE ROUGHNESS	0.1 MICRONS PER INCH	0.1 MICRONS PER INCH		1		25mm DIAMETER, NIR I COATED SAPPHIRE	
SURFACE QUALITY	80-50	80-50			TITLE	WINDOW	
BIREFRINGENCE (n _o -n _e)	0.008	0.008		1		·····	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	36550	SHEET 1 OF 1