NOTES:

1. SUBSTRATE SAPPHIRE (AI203)

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 3.5 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


S1: R(ABS) \leq 0.25% AT 880nm @ 0° AOI R(AVG) \leq 1.25% FROM 400-870nm @ 0° AOI R(AVG) \leq 1.25% FROM 890-1000nm @ 0° AOI


S2: R(ABS) \leq 0.25% AT 880nm @ 0° AOI R(AVG) \leq 1.25% FROM 400-870nm @ 0° AOI R(AVG) \leq 1.25% FROM 890-1000nm @ 0° AOI



4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

5. ROHS COMPLIANT





	\$1	\$2	
SHAPE	PLANO	PLANO	
CLEAR APERTURE	Ø11.25	Ø11.25 Ø11.25	
SURFACE FLATNESS	2λ	2λ	
SURFACE ROUGHNESS	0.1 MICRONS PER INCH	0.1 MICRONS PER INCH	
SURFACE QUALITY	80-50	80-50	
BIREFRINGENCE (n _o -n _e)	0.008	0.008	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

			■ Eamuna Optics®	
THIRD ANGLE PROJECTION	$\phi \Leftrightarrow$	TITLE	12.5mm DIAMETER, VIS-NIR COATED SAPPHIRE WINDOW	
ALL DIMS IN	mm	DWG NO	36579	SHEET 1 OF 1