




NOTES:

- 1. SUBSTRATE:
Fused Silica (Corning 7980)
- 2. TEMPERATURE RANGE:
-40 TO +170 °C

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SPECTRAL RANGE	200 - 1500nm
CLEAR APERTURE (mm)	$\varnothing 21.6 \pm 0.1$
DIFFUSING ANGLE	$2 \pm 1^\circ$
TRANSMISSION EFFICIENCY	90%



THIRD ANGLE
PROJECTION

ALL DIMS IN

mm

Edmund Optics®

TITLE

2° DIFFUSING ANGLE 25mm DIA., UV
HOLOGRAPHIC DIFFUSER

DWG NO

35693

SHEET
1 OF 1