




NOTES:

1. SUBSTRATE
MGF2
2. EXTINCTION RATIO: >10,000:1
3. BEAM DEVIATION: <3 ARCMIN
4. BEAM SEPARATION (°): 1.0 - 2.0 , 1 @ 980nm
5. DAMAGE THRESHOLD,
CW: > 500 MW/cm²
6. RoHS NOT COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

CLEAR APERTURE	Ø10
SURFACE QUALITY	20-10
TRANSMITTED WAVEFRONT	λ/4 @ 632.8nm
WAVELENGTH RANGE	130 - 7000nm



ALL DIMS IN

mm

TITLE

MGF2 ROCHON POLARIZER

DWG NO

68825

SHEET
1 OF 1