



NOTES:

1. SUBSTRATE:
II-VI Infrared ZnSe
2. CENTERING TOLERANCE:
EDGE THICKNESS VARIATION MEASURED AT THE CLEAR APERTURE OF S1
NOT TO EXCEED 12.7µm
3. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: NONE
4. FINE GROUND SURFACE
5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY
ACROSS CLEAR APERTURE
6. WAVELENGTH RANGE: 8000 - 12000nm
7. SURFACE ROUGHNESS: <50 Å
8. ROHS: COMPLIANT

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2			 Edmund Optics®			
SHAPE	CONVEX	PLANO						
RADIUS	105.200	INFINITY	EFL (AT 10.6 microns)	75.00				
SURFACE QUALITY	40-20	40-20	BFL (AT 10.6 microns)	72.71				
CLEAR APERTURE	90%	90%			SHEET 1 OF 1			
POWER at 10.6µm	λ/10	λ/10						
IRREGULARITY at 10.6µm	λ/20	λ/20			BEVEL PROTECTIVE AS NEEDED			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED						