


NOTES:

1. SUBSTRATE:
II-VI Infrared ZnSe
2. CENTERING TOLERANCE:
EDGE THICKNESS VARIATION MEASURED AT THE CLEAR APERTURE OF S1
NOT TO EXCEED 12.7µm
3. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: NONE
4. FINE GROUND SURFACE
5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY
ACROSS CLEAR APERTURE
6. WAVELENGTH RANGE: 8000 - 12000nm
7. SURFACE ROUGHNESS: <50 Å
8. ROHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2			Edmund Optics®			
SHAPE	CONVEX	PLANO						
RADIUS	280.540	INFINITY	EFL (AT 10.6 microns)	200.00				
SURFACE QUALITY	40-20	40-20	BFL (AT 10.6 microns)	198.55	50.8mm Dia. x 200mm FL, Uncoated, ZnSe Plano-Convex Lens			
CLEAR APERTURE	90%	90%	THIRD ANGLE PROJECTION					
POWER at 10.6µm	λ/10	λ/10	ALL DIMS IN	mm	DWG NO	39541	SHEET 1 OF 1	
IRREGULARITY at 10.6µm	λ/20	λ/20						
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED						