
NOTES:


- 1. SUBSTRATE: ZnSe
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 3 ARCMIN
- 3. COATING (APPLY ACROSS COATING APERTURE)

\$1& \$2: HIGH- EFFICIENCY BROADBAND (BBAR) $R(AVG) \le 3.0\%$ FROM 3 - $12\mu m$



5. RoHS: COMPLIANT





PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	40-20	40-20	
SURFACE FLATNESS @ 10.6µm	λ/20	λ/20	THIRD AN PROJECT
CLEAR APERTURE	Ø11.43	Ø11.43	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIM

THIRD ANGLE PROJECTION	$\phi \Leftrightarrow$		TIT
ALL DIMS IN	mm		D۷

Edmund Optics®)
12.7mm DIA v 1mm THICK 3 12u COATED	

1 OF 1

	TITLE	ZnSe WINDOW		
mm	DWG NO	39405	SHEET 1 OF 1	