




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



CENTER WAVELENGTH CWL (nm)	632.8
BANDWIDTH (nm)	2.4
OPTICAL DENSITY OD	\geq6.0
TRANSMISSION (%)	>90
SURFACE QUALITY	60-40
ANGLE OF INCIDENCE (°)	0 \pm2
DURABILITY (ENVIRONMENTAL)	MIL-STD-810F Paragraphs 501.4, 502.4, AND 507.4
DURABILITY (PHYSICAL)	MIL-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, AND 4.5.5.3
OD 5 BLOCKING WAVELENGTH RANGE (nm)	515-627 & 639-885
OD 6 BLOCKING WAVELENGTH RANGE (nm)	582-623 & 642-696
RoHS	COMPLIANT

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION		TITLE	632.8nm High Performance Laser Line Filter 25mm Dia.	
ALL DIMS IN	mm	DWG NO	64253	SHEET 1 OF 1