



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



FOCAL LENGTH FL (mm)	20
MAGNIFICATION	10X
MOUNTING THREAD	M26 x 36 TPI
NUMERICAL APERTURE NA	0.42
WORKING DISTANCE (mm)	15
LENGTH EXCLUDING THREADS (mm)	80
MAXIMUM DIAMETER (mm)	39
TYPE	Microscope Objective
COMPATIBLE TUBE LENS	Focal Length: 200mm
DEPTH OF FOCUS (µm)	1.55
ENTRANCE PUPIL (mm)	0
FIELD OF VIEW, 1/2" SENSOR	0.64 x 0.48mm
FIELD OF VIEW, 18 DIAMETER FIELD EYEPIECE (mm)	1.8
FIELD OF VIEW, 2/3" SENSOR	0.88 x 0.66mm
FIELD OF VIEW, 24 DIAMETER FIELD EYEPIECE (mm)	2.4
RESOLVING POWER (µm)	0.6
WAVELENGTH RANGE (nm)	435 - 655
RoHS	Exempt

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®



TITLE	10X Mitutoyo Plan Apo HR Infinity Corrected Objective		
DWG NO	58236	SHEET	1 OF 1

ALL DIMS IN

mm

DWG NO

58236

SHEET  
1 OF 1