## NOTES:


1. SUBSTRATE: FUSED SILICA


2. RoHS: COMPLIANT

3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 5 ARCMIN

4. COATING (APPLY ACROSS COATING APERTURE) \$1& \$2: 1/4 WAVE MgF2 @ 550nm R(AVG) < 1.75% FROM 400 - 700nm







## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SHAPE	\$1 PLANO	\$2 PLANO				<b>Edmund Option</b>	CS®
SURFACE ACCURACY	1λ	1λ	THIRD ANGLE PROJECTION		TITLE	30mm DIA. MgF2 COATED, 1λ FUSED SILICA WINDOW	
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	Ø27.00	Ø27.00		<u>'</u>			CLIEFT
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	11925	SHEET 1 OF 1

