



NOTES:

1. COATING (APPLY ACROSS CLEAR APERTURE)
LASER V-COAT
R(ABS) ≤ 0.25% @ 355nm
2. RoHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

DAMAGE THRESHOLD (PULSED)	2.5J/cm ² @ 10ns, 20Hz, 355nm
DESIGN WAVELENGTH DWL (nm)	355
EXPANSION POWER	20X
TRANSMISSION (%)	> 99 (NOMINAL)
NOMINAL PERFORMANCE	< λ /10 FOR 0.9mm INPUT BEAM (NOMINAL)



ALL DIMS IN mm

EO[®] Edmund Optics[®]

TITLE	20X, 355nm VEGAT [™] Nd:YAG LASER LINE BEAM EXPANDER
DWG NO	35119
SHEET	1 OF 1