NOTES:


1. SUBSTRATE: FUSED SILICA


2. RoHS: COMPLIANT

3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 5 ARCMIN

 COATING (APPLY ACROSS COATING APERTURE) \$1& \$2: R(ABS) ≤1.5% FROM 750 - 800nm R(ABS) ≤1.0% FROM 800 - 1550nm R(AVG) ≤0.7% FROM 750 - 1550nm







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SHAPE	\$1 PLANO	\$2 PLANO			B	Edmund Option	CS [®]
SURFACE ACCURACY SURFACE QUALITY	1λ 60-40	1λ 60-40	THIRD ANGLE PROJECTION		TITLE	40mm DIA. NIR II COATED, 1λ FUSED SILICA WINDOW	
CLEAR APERTURE	Ø36.00	Ø36.00					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	39302	SHEET 1 OF 1

