


NOTES:

1. SUBSTRATE:
Fused Silica
2. S2 TO BE PARALLEL TO S1 TO WITHIN <3 ARCMINS
3. COATING (APPLY ACROSS COATING APERTURE)

S1 & S2: 1030nm High Laser AR Coating
R(ABS) < 0.10% @ 1030nm @ 0° AOI

DAMAGE THRESHOLD,
PUSLED: 15 J/cm² @ 20ns , 20 Hz @ 1030nm


4. FINE GROUND SURFACE
5. CLEAR APERTURE AND COATING APERTURE ARE CENTERED ON SURFACE
6. ROHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	10-5	10-5
SURFACE FLATNESS	0.10 WAVE	0.10 WAVE
CLEAR APERTURE	Ø34.29	Ø34.29
COATING APERTURE	Ø34.29	Ø34.29
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE: 0.1R 1030nm Laser Window 38.1 Dia x 6.35

DWG NO: 11272

SHEET 1 OF 1