





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SUBSTRATE	Fused Silica
ANGLE OF INCIDENCE	0 ±2
BANDWIDTH (nm)	>250
CENTER WAVELENGTH CWL (nm)	325
OPTICAL DENSITY OD	≥6.0
SHAPE	PLANO
SURFACE QUALITY	60-40
TRANSMISSION (%)	90
EDGE STEEPNESS (nm)	2.0
TRANSITION WIDTH (nm)	5.0
CLEAR APERTURE (%)	>88
DURABILITY	Environmental: MIL-STD-810F, Physical: MIL-C-48497A
RoHS	COMPLIANT

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	25mm Dia., 248nm Laser Line Longpass Filter	
ALL DIMS IN	mm	DWG NO	12254	SHEET 1 OF 1