


NOTES:

1. SUBSTRATE:
OPAL GLASS
2. COATING
VACUUM DEPOSITED DURABLE CHROMIUM PATTERN
3. LINE PAIRS : 18-Jan
LINE WIDTH TOLERANCE (mm): ± 2.7 -1.3 μm
4. OPTICAL DENSITY: ≥ 3.0
5. CHANGES IN FREQUENCY STEPS:
1.1, 1.25, 1.4, 1.6, 1.8, 2.0, 2.2, 2.5, 2.8, 3.2, 3.6, 4.0,
4.5, 5.0, 5.6, 6.3, 7.1, 8.0, 9.0, 10.0, 11.0, 12.5, 14.0,
16.0, 18.0



PLEASE NOTE:
NBS 1963A AREA ENLARGED

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO
CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR
REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION		TITLE		1-18, 101.6 x 101.6mm NBS 1963A Negative Target, Opal	
ALL DIMS IN	mm	DWG NO	85282	SHEET 1 OF 1	