




FOCAL LENGTH (EFL): $4 \pm 0,04$

BACK FOCAL LENGTH (BFL): 3,57

- 1 AR COATING: YAG-BBAR
 $R(ABS) < 0,25\% @ 532nm @ 0^\circ AOI$
 $R(ABS) < 0,25\% @ 1064nm @ 0^\circ AOI$
 $R(AVG) < 1,0\% FROM 500-1100nm @ 0^\circ AOI$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$3,401 \pm 0,003 CX$	GLASS N-LaSF9 850/322	R	∞PL
Øe	2		Øe	2
3/	3 (0,5) $\lambda=632,8 nm$		3/	3 (0,5) $\lambda=632,8 nm$
4/	-		4/	52,94'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT SCALE: NONE $\lambda = 587,6nm$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 2,5mm Dia x 4mm FL, YAG-BBAR Coated, Plano-Convex Lens

DWG NO 35724

SHEET SIZE A4 SHEET 1 OF 1