




NOTES:

1. LASER CLASS: IIIb
SPATIAL MODE: TEM00
2. BEAM DIAMETER(mm): 1.0 Typical
BEAM DIVERGENCE(mrad): <1 Typical
3. MODULATION FREQUENCY: 0 - 10 kHz
4. OPERATING TEMPERATURE: 15 to 35 °C
OPERATING VOLTAGE: 5.0 V
5. OUTPUT POWER: 10 mW
6. WAVELENGTH RANGE: 532 ±1 nm



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION		TITLE	10mW, 532nm Fixed Focus DPSS Alignment Laser	
		DWG NO	37028	SHEET 1 OF 1