





FOCAL LENGTH (EFL): 25 ±0,25
 BACK FOCAL LENGTH (BFL): 23,22

- 1 YAG-BBAR
 R(ABS) < 0,25% @ 532nm @ 0° AOI
 R(ABS) < 0,25% @ 1064nm @ 0° AOI
 R(AVG) < 1,0% FROM 500-1100nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 12,92 CX Øe 11 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -	GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 11 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm		TITLE 12,0mm Dia, x 25,0mm FL, YAG-BBAR Coated, Plano-Convex Lens			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY							
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				SHEET SIZE A4			
INDICATIONS IN ACCORDANCE WITH ISO 10110			SHEET 1 OF 1				