




FOCAL LENGTH (EFL): 25 ±0,25

BACK FOCAL LENGTH (BFL): 22,956

1 AR COATING:

¼ WAVE MgF2 @ 550nm
R(AVG) < 1,75% FROM 400-700nm (N-BK7)

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	12,92±0,013 CX	GLASS N-BK7 517/642	R	∞ PL
Øe	11,5		Øe	11,5
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 587,6nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

12,5mm Dia, x 25,0mm FL, MgF2 Coated,
Plano-Convex Lens

DWG NO

38235

SHEET SIZE
A4

SHEET
1 OF 1