




FOCAL LENGTH (EFL): 2,5 ± 0,03
 BACK FOCAL LENGTH (BFL): 2,07

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	2,12±0,002 CX	GLASS N-LaSF9 850/322	R	∞ PL
Øe	2		Øe	2
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	52,94'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

λ = 587,6nm

FIRST ANGLE
PROJECTION



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm



Edmund Optics®

TITLE

2,5mm Dia, x 2,5mm FL, Uncoated,
Plano-Convex Lens

DWG NO

43399

SHEET SIZE
A4

SHEET
1 OF 1