





FOCAL LENGTH (EFL): 200 ±2
BACK FOCAL LENGTH (BFL): 198,02

1 AR COATING: NONE

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R	91,692±0,092 CX		GLASS FUSED SILICA 458/678	R	∞ PL	
Øe	24			Øe	24	
3/	3 (0,5) λ=632,8 nm			3/	3 (0,5) λ=632,8 nm	
4/	-			4/	2,18'	
5/	40 - 20 (MIL-PRF-13830B)			5/	40 - 20 (MIL-PRF-13830B)	
6/	-			6/	-	
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	25mm Dia, x 200mm FL Uncoated, UV Plano-Convex Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				ALL DIMS IN:	mm	
INDICATIONS IN ACCORDANCE WITH ISO 10110			DWG NO	48280	SHEET SIZE A4	SHEET 1 OF 1