


LEFT SURFACE			MATERIAL		RIGHT SURFACE			
R	24,81±0,025 CX		GLASS	N-BK7 517/642	R	∞ PL		
Øe	5,4				Øe	5,4		
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm		
4/	-				4/	1,93'		
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)		
6/	-				6/	-		
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE	6,0mm Dia, x 48,0mm FL, Uncoated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					DWG NO	45233	SHEET SIZE A4	SHEET 1 OF 1
INDICATIONS IN ACCORDANCE WITH ISO 10110								
			ALL DIMS IN:	mm				