



FOCAL LENGTH (EFL): $22 \pm 0,22$
 BACK FOCAL LENGTH (BFL): $20,73$

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$11,37 \pm 0,011$ CX	GLASS N-BK7 517/642	R	∞ PL
ϕe	8,1		ϕe	8,1
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION				
ROHS: COMPLIANT	SCALE: NONE	$\lambda = 587,6$ nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	9,0mm Dia, x 22,0mm FL, Uncoated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				ALL DIMS IN:	DWG NO	45235	SHEET SIZE
INDICATIONS IN ACCORDANCE WITH ISO 10110						SHEET	1 OF 1